

NEWTON'S RINGS
6D30.10

UV LIGHT SOURCE

NEWTON'S
RINGS
FILTER

AERO EKTAR LENS

SMALL OPTI BENCH

PLACE UV LIGHT SOURCE ~ 3 INCHES FROM THE NEWTON'S RINGS APPARATUS.

PLACE AERO EKTAR LENS ~ 18 cm FROM THE NEWTON'S RINGS APPARATUS.

PLAY WITH DISTANCES BETWEEN LAMP AND NEWTON'S RINGS UNTIL DEMO IS IN FOCUS.

DISTANCE FROM AERO EKTAR LENS TO SCREEN IS ~ 10 FEET.

